


### 6P23 6P25 6P27 6P29




# Attached Stem **SR621SW** Ф23.7

## Minute 0.40

Second 0.07 Small **0.02** 24 Hour **0.137** (Except 6P25)

1,000 pcs

case 0.45mm Clearance Clearance changes subject to the glass, case structure, and **Movement** the length of the hand. \$ 0.15 ~ 0.30mm



Month

24 Hour

High Hand Ver. 6P79

### Time measurement

### **Accuracy**

Original Package

**Balance Weight** 

<µN⋅m>

The unit (gate) time of measurement must be set at "10 sec." and the measurement must be performed in the form of complete watch.

10 sec 10 sec 10 sec

